



Product Information Sheet



Product Name: **Pred Sapphire**

Product Category: **Coloursafe**

Product Code: **PRED13**

Sizes: **7-11**

Product Description: **13 Gauge Blue HPPE/Steel/Polyester/Spandex Liner; Black PU Palm Coating**



Please scan this QR Code to view the Declarations of Conformity

These gloves were imported by: Just 1 Source & Supply Limited, York, YO60 7JX, UK

Telephone: 01653 617 7118 Website: www.just1source.com

These items comply with the requirements of the EU Regulation 2016/425 & Regulation 2016/425 on personal protective equipment, as amended to apply in GB, in line with the harmonised and designated standard(s) referenced below.

Limitations of use


EN 388:2016 + A1:2018, EN ISO 21420:2020 - The overall classification of gloves with two or more layers does not necessarily reflect the performance of the outermost layer. Gloves should not be worn when there is a risk of entanglement by moving parts or machinery.

Note – Declarations of Conformity can be found at www.just1source.com

The EN 388 test results shown below are taken from the palm area of the glove

EN388:2016 +A1:2018	Rating	Performance Levels	0	1	2	3	4	5
Abrasion (Scale 1-4)	4	Abrasion Resistance <i>Number of cycles (minimum)</i>	<100	100	500	2000	8000	n/a
Blade Cut (Coupe Test) (Scale 1-5)	X	Blade Cut <i>(Coupe Test) - Minimum</i>	<1.2	1.2	2.5	5.0	10.0	20.0
Tear (Scale 1-4)	4	Tear Resistance <i>Force (N) (Minimum)</i>	<10	10	25	50	75	n/a
Puncture (Scale 1-4)	3	Puncture Resistance <i>Force (N) (Minimum)</i>	<20	20	60	100	150	n/a
ISO 13997 (TDM) (Scale A-F)	F	ISO Cut Level <i>(N)</i>	A	B	C	D	E	F
Impact Protection (P for Pass)	Not Tested		2	5	10	15	22	30

EN388:2016 +A1:2018



4X43F

EN ISO 21420 :2020



Glove is not washable



Disposal: Dispose of used gloves as instructed by your local authority

Maintenance: Examine gloves for damages, splits and holes before each use. Always replace damaged gloves.

Donning: Insert all five fingers into the cuff of the glove and pull the cuff over your wrist until the glove is properly in place. Make sure the cuff is pulled up fully to avoid any substances or debris entering the glove.

Doffing: Pinch and lift the outside of the glove in the palm area with the opposite gloved hand; peel off while turning inside out. Hold the removed glove in the gloved hand. Slide two fingers of the ungloved hand under the remaining glove at the wrist. Peel the second glove off over the first glove and discard.

Storage: Store in dry ambient conditions, storage will not change the gloves characteristics significantly

Allergic Reactions: These gloves may cause allergic reactions, in the case of an allergic reaction please discontinue use immediately and seek medical advice. A list of substances is available on request.

Obsolescence: The shelf life of this product cannot be determined due to nature of the materials used in the composition of product, as it will be affected by many factors, such as storage conditions, usage etc.

Intended Use: This glove offers good protection against cut, tear, abrasion and puncture on the palm in dry conditions. Whilst maintaining good dexterity. This glove is not suitable for use with liquids. Ideal for use in Automotive, Component Handling, Construction, Engineering, Fabrication, Sheet Metal Manufacturing.



UKCA Type Certification issued by **ITS Testing Services (UK) Ltd**,
Centre Court, Meridian Business Park, Leicester, LE19 1WD –
Approved Body 0362



EU Type Certification issued by **Intertek Italia Spa**, Via Guido
Miglioli, 2/A – 20063 Cernusco sul Naliggio (MI) Italia – **Notified**
Body 2575