



# Product Information Sheet



Product Name: **Pred Impact**

Product Category: **Specialist**

Product Code: **TS4**

Sizes: **8-11**

Product Description: **18 Gauge Nylon/Spandex/HPPE/Steel Liner; PPU Polymer Palm Coated Glove**



Please scan this QR Code to view the Declarations of Conformity

These gloves were imported by: Just 1 Source & Supply Limited, York, YO60 7JX, UK

Telephone: 01653 617 7118 Website: [www.just1source.com](http://www.just1source.com)

These items comply with the requirements of the EU Regulation 2016/425 & Regulation 2016/425 on personal protective equipment, as amended to apply in GB, in line with the harmonised and designated standard(s) referenced below.


### Limitations of use

EN 388:2016 + A1:2018; EN407:2020; EN ISO 21420:2020 - The overall classification of gloves with two or more layers does not necessarily reflect the performance of the outermost layer. Gloves should not be worn when there is a risk of entanglement by moving parts or machinery.

**Note** – Declarations of Conformity can be found at [www.just1source.com](http://www.just1source.com)

The EN 388 test results shown below are taken from the palm area of the glove								
<b>EN388:2016 +A1:2018</b>	<b>Performance Level</b>	<b>Performance Levels</b>	<b>0</b>	<b>1</b>	<b>2</b>	<b>3</b>	<b>4</b>	<b>5</b>
<b>Abrasion</b> (Scale 1-4)	<b>4</b>	<b>Abrasion Resistance</b> <i>Number of cycles(minimum)</i>	<10 0	100	5 0 0	200 0	800 0	n/a
<b>Blade Cut (Coupe Test)</b> (Scale 1-5)	<b>X</b>	<b>Blade Cut (Coupe Test) - Minimum</b>	<1. 2	1.2	2. 5	5.0	10. 0	20. 0
<b>Tear</b> (Scale 1-4)	<b>4</b>	<b>Tear Resistance</b> <i>Force (N) (Minimum)</i>	<10	10	2 5	50	75	n/a
<b>Puncture</b> (Scale 1-4)	<b>2</b>	<b>Puncture Resistance</b> <i>Force (N) (Minimum)</i>	<20	20	6 0	100	150	n/a
<b>ISO 13997 (TDM)</b> (Scale A-F)	<b>F</b>	<b>ISO Cut Level (N)</b>	<b>A</b>	<b>B</b>	<b>C</b>	<b>D</b>	<b>E</b>	<b>F</b>
			2	5	1 0	15	22	30
<b>Impact Protection</b> (P for Pass)	<b>P</b>							

EN388:2016 +A1:2018



4X42FP

EN ISO 21420 :2020



Glove is not washable



**Disposal:** Dispose of used gloves as instructed by your local authority

**Maintenance:** Examine gloves for damages, splits and holes before each use. Always replace damaged gloves. Gloves may lose their insulative properties when wet. Due to the nature of this product the user is advised to carry out their own risk assessment.

**Donning:** Insert all five fingers into the cuff of the glove and pull the cuff over your wrist until the glove is properly in place. Make sure the cuff is pulled up fully to avoid any substances or debris entering the glove.

**Doffing:** Pinch and lift the outside of the glove in the palm area with the opposite gloved hand; peel off while turning inside out. Hold the removed glove in the gloved hand. Slide two fingers of the ungloved hand under the remaining glove at the wrist. Peel the second glove off over the first glove and discard.

**Storage:** Store in dry ambient conditions, storage will not change the gloves characteristics significantly

**Allergic Reactions:** These gloves may cause allergic reactions, in the case of an allergic reaction please discontinue use immediately and seek medical advice. A list of substances is available on request.

**Obsolescence:** The shelf life of this product cannot be determined due to nature of the materials used in the composition of product, as it will be affected by many factors, such as storage conditions, usage etc.

**Intended Use:** This glove is designed for cold working environment, as well as being able to be used to handle hot objects up to temperatures of 250°C for a maximum of 15 seconds. Whilst still offering good abrasion, tear & puncture resistance. Ideal for use in Automotive, Extrication, Fabrication, Food Industry, Glass/Glazing, High Pressure Cut Applications, Touchscreens.

The EN 407 test results shown below are taken from the palm area of the glove						
EN407:2020	Rating	Performance Levels	1	2	3	4
<b>Limited Flame Spread</b> (Scale 0-4)	X	After flame-seconds	≤15	≤10	≤3	≤2
		After glove -seconds	Infinity	≤120	≤25	≤5
<b>Contact Heat</b> (Scale 0-4)	2	Threshold ≥ 15°C	100	250	350	500
<b>Convective Heat</b> (Scale 0-4)	X	Seconds	≥4	≥7	≥10	≥18
<b>Radiant Heat</b> (Scale 0-4)	X	Seconds	≥7	≥20	≥50	≥95
<b>Small Molten Splash</b> (Scale 0-4)	X	0.5 Grams Droplet	≥10	≥15	≥25	≥35
<b>Large Molten Splash</b> (Scale 0-4)	X	Molton Iron Grams	30	60	120	200

EN407:2020



X2XXXX

**X:** Not tested

**Note:** No flame protection is claimed & the glove shall not come into contact with a naked flame  
Under the above standard product can be used to handle hot objects up to a temperature of 250 °C for a maximum of 15 seconds

These gloves have been tested and approved for use in food industries, under BS EN 1186.  
For use with foods that are hydrophilic and/or acidic nature

